

Pulp Disintegrator

RL-DSG-A



RYCOLAB

For disintegration of pulp suspensions according to different standards. Lightweight pot made from acrylic glass or heavy stainless steel pot.

Contents Include

- Disintegrator
- Acrylic pot
- Measuring gauge
- Calibration certificate
- Operation manual
- Connection cable

SPECIFICATIONS

- Made from robust stainless steel and aluminium
- Hinged head for easy take-out of the vessel
- Safety interlock
- Motor: 370 W
- Digital display of the revolutions
- Agitator speed according to standard:
 - $2,980 \pm 30$ rpm applicable for TAPPI and ISO
- Electric: 230 V- 50
- Machine Dimensions
 - 270 x 400 x 460 mm (W x L x H)
 - 36 Kg
- Shipping Dimensions:
 - 350 x 500 x 600 mm (W x L x H)
 - 56 Kg

STANDARDS

- ISO 5263-1
- SCAN C18 M2
- TAPPI T205
- PAPTAC C.6



Thwing-Albert
Instrument Company



TA060722

thwingalbert.com